

For use with LMV-D3-MP.MHS and NMV-D3-MP.MHS compact volume controllers.



OLD ZTH-EU.MHS

NEW LINK.10.MHS

- Belimo have now discontinued production of the ZTH-EU.MHS service and calibration tool. If you have an existing ZTH-EU.MHS tool you can continue to use it as normal.
- The new replacement will now be the LINK.10-MHS interface unit which will work in conjunction with the Belimo **Assistant 2 App** and your mobile phone.
- With the LINK.10-MHS interface you will now be able to see and adjust all the VAV settings directly on your mobile screen.

The Belimo **Assistance 2 App** is free to download and can be obtained directly from the Google Play Store (android) or Apple App store (iPhone) depending on the type of mobile you have.

The Belimo **Assistance 2 App** connects via your mobile phone's Bluetooth to the LINK.10 adaptor which is then connected directly to the LMV-D3-MP.MHS with the ZK1-GEN connection cable (ZK1 cable supplied with the LINK.10-MHS). Once connected the Belimo **Assistance 2** phone APP will make all the LMV-D3-MP.MHS volume settings accessible and changeable through the App. With this method you can be several metres away from LMV-D3 and the App will still connect to the LINK.10-MHS interface, this makes setting all the LMV-D3-MP.MHS parameters far easier.

NOTE:- If you need to make any adjustments to the V-Nom calibration pressure or volume settings in the LMV-D3-MP.MHS you will need a special release code from MHServices

This code along with full instructions is available from MHServices.

For full technical details on any of these products please visit MHServices web site:-

www.mhservices.co.uk

Or call 01344 780344 for technical support