



# Replacement of ZTH-EU.MHS calibration tool with new LINK.10-MHS

Data Sheet

03-26

For use with LMV-D3-MP.MHS and NMV-D3-MP.MHS compact volume controllers.



**OLD ZTH-EU.MHS**



**NEW LINK.10-MHS**

(supplied with ZK1-GEN connection cable for convenient set up)

**Belimo have discontinued production of the ZTH-EU.MHS\* service and calibration tool. The replacement is the LINK.10-MHS interface unit which works in conjunction with the Belimo Assistant 2 App on your mobile phone.**

\*If you have an existing ZTH-EU.MHS tool you can continue to use this, and we will continue to support this product technically.

The Belimo Assistance 2 App is free to download and can be obtained directly from the Google Play Store (android) or Apple App store (iPhone).

## OPERATION MADE EASY VIA YOUR MOBILE PHONE

- The Belimo Assistance 2 App connects via your mobile phones' Bluetooth to the LINK.10-MHS
- The LINK.10-MHS is plugged directly into the LMV/NMV actuator with the ZK1-GEN connection cable that is supplied with the LINK.10-MHS
- Once connected, you can be several metres away from the actuator you are calibrating which makes the set-up more convenient and secure
- The Belimo Assistance 2 App allows you to access and change all the necessary VAV volume settings directly through the App, these include:
  - VNom – pressure calibration\*
  - VNom – volume\*
  - VMax – volume
  - VMin – volume
  - Direction of rotation to open
  - 0-10V or 2-10V operation

\* If you need to make any adjustments to the V-Nom calibration pressure or volume settings you will need a special release code from MHS. This code, along with full instructions, is available from MHS on purchasing a LINK.10-MHS

**For full technical details on any of these products please visit MHServices web site [www.mhservices.co.uk](http://www.mhservices.co.uk)  
Or call 01344 780344 for technical support**